

One-touch IN/OUT connection. Possible to use in vacuum to –100 kPa





Applicable Tubing

Tubing material	FEP, PFA, Nylon, Soft nylon (1), Polyurethane
Tubing O.D.	ø3.2, ø4, ø6, ø8, ø10, ø12, ø16

Note 1) Soft nylon tubing is not compatible with water.

Product's Color

Series	Body	Release button
Series KQ2	White	Light gray
Series KQ	Black	Blue

Specifications

Fluid		Air/Water (2)				
Operating press	sure range (3)	-100 kPa to 1 MPa				
Proof pressure		3 MPa				
Ambient and flu	id temperature	-5 to 60°C, Water: 0 to 40°C (No freezing)				
	Mounting section	JIS B0203 (Taper thread for piping)				
Thread	Woulding section	JIS B0205 (Metric coarse thread)				
	Nut section	JIS B0205 (Metric fine thread)				
Seal on the thre	ads	With sealant or none				

Note 2) The surge pressure must be under the maximum operating pressure.

Note 3) Do not use the fittings with a leak tester or for vacuum retention because they are not guaranteed for zero leakage.

Principal Parts Material

Body	C3604, PBT, PP
Stud	C3604 (Thread portion)
Chuck	Stainless steel 304
Guide	Stainless steel 304, C3604, PBT
Collet, Release button	POM
Seal, O-ring	NBR
Gasket	Stainless steel 304, NBR




Series KQ2

Branch "Y": KQ2U



Applicable tubing O.D. (mm)	Connection thread Uni One-touch fittings	Model	H (width across flats)	ø D1	L	Р	A *	М	(m	ve area m²) Urethane	Mass (g)
4	1/8	KQ2U04-U01	11	10.4	40	10.4	36	16	4.2	4.2	11
-	1/4	KQ2U04-U02	14	10.4	42						16
	1/8	KQ2U06-U01	13	12.8	43.5	12.8	39.5	17	13.4	13.4	14
6	1/4	KQ2U06-U02	14		45		39				18
	3/8	KQ2U06-U03	17		46		40				26
	1/8	KQ2U08-U01	17	15.2	50.5	15.2	46.5	18.5	25.6	17.7	27
8	1/4	KQ2U08-U02			52		46				25
	3/8	KQ2U08-U03			51.5		45.5				28
	1/4	KQ2U10-U02	19	18.5	57.5	18.5	51.5	21	40	28.4	38
10	3/8	KQ2U10-U03									36
	1/2	KQ2U10-U04	22		59		51				51
12	1/4	KQ2U12-U02	22	20.9	61	20.9	55	22	57.4	45.4	53
	3/8	KQ2U12-U03			01						52
	1/2	KQ2U12-U04			62.5		54.5				52




Note 1) øD: Max. diameter

Extended Male Elbow: KQ2W



Applicable tubing O.D.	Connection thread Uni One-touch	Model	H (width	ø D1	ø D2	L1	L2	A *	М	Effective area (mm²)		Mass
(mm)	fittings		flats)							Nylon	Urethane	(g)
4	1/8	KQ2W04-U01	10	10.4	10	18	34.5	35.5 38.5	10	4.0	4.0	16
	1/4	KQ2W04-U02	14				37		16			26
	1/8	KQ2W06-U01	10				38.5	41				18
6	1/4	KQ2W06-U02	14	12.8	10	20	40.5	41	17	10.9	10.9	29
	3/8	KQ2W06-U03	17				41.5	42				40
	1/8	KQ2W08-U01	12				43.5	46.5				28
8	1/4	KQ2W08-U02	14	15.2	12	23	45.5	47	18	20.5	14.2	35
	3/8	KQ2W08-U03	17				46	48				46
	1/4	KQ2W10-U02	17	18.5	17	26.5	52.5	56 21	21	33.5	23.8	67
10	3/8	KQ2W10-U03	17									57
	1/2	KQ2W10-U04	22				54.5					98
12	1/4	KQ2W12-U02	17		17	28.5	54	58.5	22	47.7	37.7	69
	3/8	KQ2W12-U03	''	20.9								59
	1/2	KQ2W12-U04	22				56					99



Note 1) øD1: Max. diameter

^{*} Reference dimensions after Uni thread installation.

^{*} Reference dimensions after Uni thread installation.