








222 Series

Lever Connectors




222 Series	
Technical Data	
0.08 - 2.5mm ²	solid & stranded
0.08 - 4mm ²	fine-stranded
400 V/4 kV/2 ^ø	
32 A	
 9 - 10 mm	


Description.	Item No.	Box Unit.
 2-conductor	222-412	50
 3-conductor	222-413	50
 5-conductor	222-415	40

222 Series		
Accessories		
Description.	Item No.	Box Unit.
 Mounting Carrier	222-500	10
 Strain Relief Plate	222-505	10
 Angled DIN-rail adapter	222-510	10


Operating



1. Strip the conductor 9 - 10mm.



2. Open clamping unit using the lever and insert the conductor.



3. Lower the lever to close the clamp to complete the connection.
4. To remove, lift the lever and pull out the conductor.


Advantages & Accessories



Test slot

Back of the housing

- Easy testing while installed



WAGOBOX

- Suitable for the 222 and 773 Series
- Can be used within maintenance free applications



222-500 Mounting Carrier

With various mounting options

- Horizontal & vertical mounting on DIN 35 rail
- Horizontal screw mounting with strain relief plate