

PSRL FILTER FOR G-SPARK TECH SET

Item #	EAN	Product
866421	3660338205415	G-SPARK TECH

Description

Reusable Solid Particulate and Liquid Filter

Polyamide and paper filter.

Protection factor: 20

Diameter: 130mm

Water resistance: TH2

The filter of the stand-alone G-SPARK TECH filtration unit ensures filtration of solid and liquid particles in the environment close to the operator.

The filter must be used together with the pre-filter.

The filter and the pre-filter must be replaced depending on the triggering of the visual and audible clogging alarm (see G-SPARK TECH user manual). On the other hand, the filter must imperatively be replaced every 180 hours of use, in order to avoid the development of bacteria. It is advisable to replace the pre-filter every 40 hours in order to facilitate the air flow and to preserve autonomy.

The filter and pre-filter should be replaced, not cleaned. Cleaning is prohibited in order not to damage the filter and the pre-filter, and not to disturb the calibration of the clogging alarm.

The filter is tested and certified with, and only with, the standalone G-SPARK TECH filtration unit.

The stand-alone filtration unit G-SPARK TECH is tested and certified according to EN 12941 with, and only with, the filter.



Standards and certifications

Standard EN 12941