



MASTER PL-T 4 Pin

MASTER PL-T 18W/840/4P 1CT/5X10BOX

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

Product data

General Information	
Cap-Base	GX24Q-2 [GX24q-2]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	1200 lm
Luminous Flux (Rated) (Nom)	1200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	67 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	86 %
LLMF 8000 h Rated	84 %

LLMF 12000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	16.5 W
Lamp Current (Nom)	0.210 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4 Pins
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	20 kWh

MASTER PL-T 4 Pin


Product Data	
Full product code	871150061099770
Order product name	MASTER PL-T 18W/840/4P 1CT/5X10BOX
EAN/UPC - Product	8711500610997
Order code	927914484071
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	50
Material Nr. (12NC)	927914484071
Net Weight (Piece)	58.000 g
ILCOS Code	FSM-18/40/1B-E-GX24q=2

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




PL-T 18W/840/4P M

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/840/4P 1CT/ 5X10BOX	41.0 mm	71.7 mm	96.0 mm	111.7 mm

Photometric data





Lightcolor /840




Lightcolor /840

MASTER PL-T 4 Pin


Lifetime



Life Expectancy 3 h cycle



Life Expectancy 12 h cycle



Lumen Maintenance 3 h and 12 h cycle

