

Compact Pressure Switch

Series ZSE2/ISE2

How to Order

Operating pressure range/ Setting pressure range

Nil	0 to 1 MPa
L	0 to 100 kPa

Piping specifications

01	Single mounting R $\frac{1}{8}$ (Note 1)
T1	Single mounting NPTF $\frac{1}{8}$ (Note 1)

Note 1) M5 x 0.8 (female) threaded.

**Positive
pressure**

ISE2

Vacuum

ZSE2

Piping specifications

01	Single mounting R $\frac{1}{8}$ (Note 2)
T1	Single mounting NPTF $\frac{1}{8}$ (Note 2)
0X	W/suction filter (Mounting on ZX unit) M5 x 0.8
0XY	W/suction filter (Mounting on ZX unit) M6 x 1 (Option)
0R	Base mounting (Mounting on ZR unit)

Note 2) Single mounting type: M5 x 0.8 (female) threaded.

Wiring specifications

Nil	Grommet type (Lead wire: 0.6 m)
L	Grommet type (Lead wire: 3 m)
C	Connector type (Lead wire: 0.6 m)
CL	Connector type (Lead wire: 3 m)
CN	Without connector

Output specifications

15	NPN open collector
55	PNP open collector

With Connector/How to Order

- Without lead wire (Connector 1 pc., Socket 3 pcs.) **ZS-10-A**
- With lead wire **ZS-10-5A-**

Note) When ordering switch with
5 m long lead wire, indicate
both part numbers.

Ex.) ZSE2-01-15CN 1 pc.
ZS-10-5 A-50 1 pc.

Lead wire length

Nil	0.6 m
30	3 m
50	5 m

Replacement Element (Filter) Part Number (Refer to page 843)

- Filter vessel assembly (Filter vessel, Filter element) **ZX1-FK-PC**
- Filter element **ZX1-FE**
- Filter gasket **ZX1-FG**